



## BMP-YLK1



## Installation Guide

**Product Note:** The YoLink® Hub is currently available in two sizes. This mount is specifically designed for the YoLink® Hub measuring **4.33" x 4.33"** square. It will not work with the smaller YoLink® Hub which measures **3.38" x 3.38"** square. Please check the size of your YoLink® Hub before ordering to insure proper fit.


**Altelix LLC USA: 866-660-WIFI (9434) International: +1 561-660-9434 sales@altelix.com www.altelix.com**

Copyright (C) 2023 Altelix LLC. All rights reserved. Altelix and the Altelix logo are Trademarks and/or Registered Trademarks of Altelix LLC.

Specifications are subject to change without notice. See [www.altelix.com](http://www.altelix.com) for most current information

# BMP-YLK1 Installation Guide

The BMP-YLK1 can be directly mounted to the inside of a network equipment cabinet using the included double-sided tape. For wall mounting, wall anchors and screws are also provided.



To use the included double-sided tape, firmly attach to the rear of the BMP-YLK1 as shown.

For wall mounting use the drill template below.



Once the BMP-YLK1 is mounted, insert the YoLink Hub into the cradle as shown.

**Installation Note:** If attaching to surfaces such as glass, mirror and tile, be sure to clean surfaces first with alcohol wipes or glass cleaner

Place the template in the desired mounting location and mark the holes. Follow all applicable safety precautions when drilling. If necessary, drill pilot holes where you made your mark. If you will be using the wall anchors provided with your enclosure drill 3/16 inch holes. If you will be using the screws directly, drill 3/32 inch holes.

## Drill Template for Mounting Holes



## Printing Instructions

Print onto 8-1/2" x 11" paper. Select "Actual Size" or "100% Scale" when printing.